

The 130/131 contact thermometers offer fast response and laboratory accuracy. These thermometers offer 0.1°C/0.1°F resolution over the entire measurement ranges. A rugged holster protects both models.

- Easy to use: Remove the protective sheath, press the ON/OFF button and insert into the testing area.
- LCD screen shows readings in Fahrenheit or Celsius
- Range: -40° to +250° C/ -40° to +482° F
- 132 is pen type humidity & temperature meter

High Accuracy

Faster Reaction time 6s (133A)



EMC
EN: 61326
EN: 60825-1



Model 133A

| Features | | | | | | |
|------------------------------------|-------|-------|---------|-------|-----|-------|
| | 130 | 130A | 131/133 | 131A | 132 | 133A |
| User Selectable °C or °F | * | * | * | * | * | * |
| Resolution 0.1°C/0.1°F | * | * | * | * | * | * |
| Sampling time 2.0 seconds | * | 0.5S | * | 0.5S | * | 0.5s |
| Reaction time | 10s | 6s | 10s | 6s | 10s | 6s |
| LCD display | * | * | * | * | * | * |
| Max / Min Hold and Data Hold | | | * | | * | * |
| Auto Power Off | * | * | * | * | * | * |
| Humidity & Temperature measurement | Temp. | Temp. | Temp. | Temp. | * | Temp. |
| 2.0mm Diameter probe shaft tip | | * | | * | | * |



| Specifications | | | | | | | | |
|----------------|-----------------|----------------|------|------|------|-----|---------|-----|
| Function | Range | Basic Accuracy | 130A | 131A | 133A | 130 | 131/133 | 132 |
| Temperature | -40~250°C/482°F | ±1.5% | | | | * | * | * |
| | -40~200°C/392°F | ±1.0% | * | * | * | | | |
| Humidity | 10%RH~95%RH | ±3.5% | | | | | | * |

Size(HxWxD): 130:150mm x 40mm x 28mm
131/132/133:211mm x 32mm x 19mm

Weight: 130:19g
131/132/133:35g

Accessories :
One LR44(1.5V) button battery and clamshell.



Model 132



Model 130



Model 133



Model 131